


C14 and C16 IEC Inlet - Vertical

VERTICAL MODULE ARRANGEMENT



- Inlet with 2.8mm or 6.3mm tags
- Double Pole Switch/ Fuseholder/Indicator/ Voltage Selectors/ Blanking Plate
- Filtered Inlet Option
- Options of I/O marked switches



How to Order

**BZV xx / xxxxx / xx**

Type of Inlet / Outlet	Filtered or Non Filtered Inlet	Combination of Other Components	
<p>C14 Power Inlet (cold condition), 6.3 or 2.8mm tabs:</p> <p><b>03</b> = PX0575/63 <b>04</b> = PX0575/28</p> <p>C16 Power Inlet (hot condition), 6.3 or 2.8mm tabs:</p> <p><b>05</b> = PX0595/63 <b>06</b> = PX0595/28</p>	<p>Z0000 = Non Filtered Axxxx = Standard Bxxxx = Medical</p>	<p>Twin Fuseholder and Double Pole Switch: <b>05</b> = 2 x FX0359 + D.P. Switch</p> <p>Twin Fuseholder and Double Pole Neon Switch: <b>06</b> = 2 x FX0359 + D.P. Red Neon Switch <b>09</b> = 2 x FX0359 + D.P. Green Neon Switch <b>19</b> = 2 x FX0359 + D.P. Red Neon Switch 125V</p> <p>Twin Fuseholder and Neon Indicator: <b>07</b> = 2 x FX0359 + Red Neon Indicator</p> <p>Voltage Selector, Fuseholder and Double Pole Switch: <b>15</b> = 1 x VS0001 + 1 x FX0359 + Double Pole switch</p> <p>Voltage Selector, Fuseholder and Double Pole Neon Switch: <b>16</b> = 1 x VS0001 + 1 x FX0359 + D.P. Red Neon Switch <b>18</b> = 1 x VS0001 + 1 x FX0359 + D.P. Green Neon Switch</p> <p>Voltage Selector, Fuseholder and Neon Indicator: <b>17</b> = 1 x VS0001 + 1 x FX0359 + Red Neon Indicator</p> <p>Twin Fuseholder and Double Pole High Inrush Switch: <b>20</b> = 2 x FX0359 + D.P. High Inrush Switch</p> <p>Twin Fuseholder and Double Pole High Inrush Neon Switch: <b>21</b> = 2 x FX0359 + 1 x D.P. High Inrush Green Neon Switch <b>22</b> = 2 x FX0359 + 1 x D.P. High Inrush Red Neon Switch</p>	<p>Voltage Selector, Neon Indicator and Double Pole Switch <b>25</b> = 1 x VS0001 + 1 x DX0928/110V/Red + D.P. Switch <b>26</b> = 1 x VS0001 + 1 x DX0928/110V/Green + D.P. Switch <b>27</b> = 1 x VS0001 + 1 x DX0928/250V/Red + D.P. Switch <b>28</b> = 1 x VS0001 + 1 x DX0928/250V/Green + D.P. Switch</p> <p>Voltage Selector, Neon Indicator and Double Pole High Inrush Switch: <b>29</b> = 1 x VS0001 + 1 x DX0928/250V/Red + D.P. High Inrush Switch <b>30</b> = 1 x VS0001 + 1 x DX0928/250V/Green + D.P. High Inrush Switch</p> <p>Fuseholder, Neon Indicator and Double Pole Switch <b>31</b> = 1 x FX0359 + 1 x DX0928/110V/Red + D.P. Switch <b>32</b> = 1 x FX0359 + 1 x DX0928/110V/Green + D.P. Switch <b>33</b> = 1 x FX0359 + 1 x DX0928/250V/Red + D.P. Switch <b>34</b> = 1 x Fx0359 + 1 x DX0928/250V/Green + D.P. Switch</p> <p>Fuseholder, Neon Indicator and Double Pole High Inrush Switch: <b>35</b> = 1 x FX0359 + 1 x DX0928/250V/Red + D.P. High Inrush Switch <b>36</b> = 1 x FX0359 + 1 x DX0928/250V/Green + D.P. High Inrush Switch</p> <p>Fuseholder, Blanking Plate and Double Pole High Inrush Neon Switch: <b>47</b> = 1 x FX0359 + 1 x Blanking Plate (Right) + D.P. High Inrush Green Neon Switch</p> <p>Fuseholder, Blanking Plate and Double Pole Switch: <b>48</b> = 1 x FX0359 + 1 x Blanking Plate (Right) + D.P. Switch</p>
<p>Please note type 05 and 06 are not available in filtered version</p>	<p>For Filtered inlet use 6th to 9th characters from filter ordering code see pages 125-126.</p> <p>E.g. BZV03/<b>A0120</b>/07</p>		

IEC CONNECTORS